

Order Toll Free: 1-800-872-3684 Order by FAX: 1-610-436-4983 www.thesafetyhouse.com



HOW DO PLASTICS FIT INTO YOUR Asbestos Hoatement?



CONTAINMENT - You will need to contain your asbestos debris by constructing a plastic containment around the ceiling areas you wish to remove. This is accomplished by covering walls and floors within the project room or rooms to ensure all debris is captured and remains on the plastic sheeting during removal.

Click here to see our full line of Plastic Poly Sheeting.

Size	4MIL	5MIL	6MIL
10" x 100"	PC0092	PC0110	PC0091
12" x 100"	PC0102	PC0103	PC0104
20" x 100"	PC0090	PC0095	PC0096

Disposable Shower Enclosures

REMOVAL - Asbestos waste disposal bags: These bags will be used for containing asbestos contaminated debris and materials. The bags come in various sizes and mil thicknesses. Each should be pre-printed with required asbestos warnings. *Click here to see our full line of Asbestos Removal Bags*.

Size	Industrial (3.5MIL)	Full Weight	6MIL SPEC
30" x 40"	BA999 100/case	BA1017 100/case	BA1016 75/case
33" x 50"	BA998 75/case	BA1002 75/case	BA1025 75/case
33" x 50"	BA1011 100/roll	BA1002R 75/roll	BA1026 75/roll
36" x 60"	BA1012 50/case	BA1020 50/case	BA1028 50/case

Extended Run Glove Bags



DISPOSABLE SHOWER ENCLOSURES - A D-Con shower enclosure system assembles in just minutes. The newly assembled airlock system looks clean and professional and reflects well on the contractor. And because it is disposable, there are no cleaning, transportation or storage costs associated with the unit after the project is complete.

Click here to see our full line of Disposable Shower Enclosures.

		•		
DC0119FR		DC0121	Shower Head Assembly	
Flame Retardant		DC0120	Replacement Poles	
DC0101 Disposable 3-Stage 48" x 48"				

EXTENDED RUN GLOVE BAGS - The revolutionary way to tackle extended run sections of pipe insulation. Dramatically increase productivity and safety by eliminating multiple bag set-up time and reducing jobsite fiber counts. Use in sections of 2 to 25 chambers at a time. Dispenses quickly and easily while protecting unused bags from contamination.

Click here to see our full line of Extended Run Glove Bags.

	GB0100	44" x 60" Single Glove Bags	GB0106	60" x 72" Continuous Glove Bags
	GB0102	44" x 60" Continuous Glove Bags	GB0108	72" x 120" Continuous Glove Bags